

DUPLI-COLOR TUNING TRANSPARENT SPRAY

Ord.-no.: look at ordering information



Technical Information

Transparent-Spray is suitable for application on numerous transparent objects, which you want to give colour, while you want to keep the transparency resp. the structure of the ground. Examples: glass, transparent coatable plastics, wood, lamps, bulbs, metals etc. Attention: The use on motor vehicles in the area of lightening and windows is in many countries not allowed!

Quality & properties

- High-grade nitro-combi quality
- Transparent; the structure of the ground remains visible after coating
- Excellent adhesion
- Very good colour retention (light-proof, non-yellowing)
- Scratch-, shock- and impact-resistant
- Durable gloss
- Quick-drying
- Good flow, smooth surface
- Weather-resistant
- High surface hardness and good elasticity

Physical & chemical data

- Base: Nitrocombi resin
- Colourname:
 - ◊ transparent blue
 - ◊ transparent yellow
 - ◊ transparent green
 - ◊ transparent orange
 - ◊ transparent red
 - ◊ transparent black
- Smell: Characteristic
- Degree of gloss: gloss, >75 GU
- Efficiency: 150 ML – 0.5 m²
- Dry to touch: 50 min
- Dust dry: 10 min
- Overcoatable: 1 h
- Surfaces: glass, transparent coatable plastics, wood, lamps, bulbs, metals etc.
- Minimum Working Temperature: 10 °C
- Maximum Working Temperature: 25 °C
- Vapour pressure: 8300/20 bar
- Storage stability: 10 y
- Content: 150 ML

How to use

- Prime plastic parts with the colourless DUPLI-COLOR Tuning Plastic Primer.
- The surface has to be clean, dry and free from fat.
- Protect surrounding area from spray mist!
- Before use, shake the can vigorously for 3 minutes.
- The spray distance should be approx. 20-30 cm.
- Spray several thin coats in 3 - 5 minute intervals onto the dry repair spot, till the desired effect is achieved.
- Before lacquering lightening bulbs you should make a test, as the adhesion cannot be granted up to every temperature level.
- Do not spray over synthetic paints!

Environmentally sound

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

Marking/Labelling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

For any further technical questions call our hotline +49 (0) 62 66 75-266 from Monday to Thursday from 9 h a.m. to 3 h p.m. or on Friday until 12 h p.m.

As of August 18, 2022 – This release replaces all eventually earlier issued versions.

European Aerosols GmbH, Kurt-Vogelsang-Straße 6, 74855 Haßmersheim - info-de@european-aerosols.com
European Aerosols B.V., Wolfraamweg 2, NL-8471 XC Wolvega - info-nl@european-aerosols.com