

## DUPLI-COLOR INOX LOOK

Ord.-no.: 516238

### Technical Information



Quick- and hard-drying special lacquer to create valuable inox-effect. Scratch-, shock- and bump-proof. For metal, wood, glass, ceramics and others, e.g. picture frames, light switches, shelves, banisters, chairs etc. Color: inox.

#### Quality & properties

- High-grade nitro-combi quality
- Very good coverage
- Excellent adhesion on many surfaces
- Good flow, smooth surface
- Quick-drying
- Suitable for indoors and outdoors applications
- Weather-resistant, light-proof, UV-resistant
- Scratch-, shock- and impact-resistant
- Resistant to engine oils, diluted cleansers etc.

#### Physical & chemical data

- Base: Acrylic resin
- Colourname: silver
- Smell: Characteristic
- Degree of gloss: mat, 10 ±2 GU
- Efficiency: 400 ML – 1.2 m<sup>2</sup>
- Dry to touch: 30 min
- Dust dry: 10 min
- Completely dry: 24 h
- Surfaces: metal, wood, glass, ceramics, paper, stone etc.
- Minimum Working Temperature: 10 °C
- Maximum Working Temperature: 25 °C
- Vapour pressure: 8300/20 bar
- Storage stability: 10 y
- Content: 400 ML

#### How to use

- If necessary, equalize uneven surfaces (fill, sand, prime)
- The surface has to be clean, dry and free from fat.
- Cover areas not to be painted.
- Before use, shake the can for 2-3 minutes.
- Test spray at an invisible spot to check colour-matching and compatibility of the lacquer.
- Spray from a distance of approx. 25 cm several thin coats.
- Do not spray over synthetic paints!

#### Environmentally sound

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

#### Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

#### Marking/Labeling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

For any further technical questions call our hotline +49 (0) 62 66 75-266 from Monday to Thursday from 9 h a.m. to 3 h p.m. or on Friday until 12 h p.m.

As of August 18, 2022 – This release replaces all eventually earlier issued versions.