

DUPLI-COLOR METALLIC LOOK

Ord.-no.: look at ordering information

Technical Information



DUPLI-COLOR METALLIC LOOK is a quick-drying lacquer with special effect pigments. It can be used on nearly all kinds of surfaces, such as metal, wood stone, glass, ceramics, paper, carton. High-grade acrylic quality. The colour silver is also available in synthetic quality.

Quality & properties

- High-grade acrylic nitrocombi quality
- Very good coverage
- Durable gloss Can be polished after coating with 2-coat clear lacquer
- Excellent adhesion
- Quick-drying
- Good flow, smooth surface High surface hardness and good elasticity
- Limited resistance to petrol
- After coating with clear lacquer weather-resistant
- Very good colour retention (light-proof, non-yellowing)
- Scratch-, shock- and impact-resistant

Physical & chemical data

- Base: Acrylic resin
- Colourname:
 - ◊ blue
 - ◊ silver
 - ◊ green
 - ◊ gold
 - ◊ lilac
 - ◊ purple
 - ◊ red
 - ◊ black
- Smell: Characteristic
- Degree of gloss: semi mat, 25 ±5 GU
- Efficiency:
 - ◊ 400 ML – 1.3 m²
 - ◊ 200 ML – 0.6 m²
 - ◊ 12 ML – small spots
- Dry to touch: 30 min
- Dust dry: 10 min
- Completely dry: 24 h
- Overcoatable: 30 min
- Surfaces: metal, wood stone, glass, ceramics, paper, carton and on coatable hard plastics
- Minimum Working Temperature: 10 °C
- Maximum Working Temperature: 25 °C
- Vapour pressure:
 - ◊ 8300/20 bar
 - ◊ 13/20 bar
- Flash point: 27 °C
- Storage stability: 10 y
- Content:
 - ◊ 400 ML
 - ◊ 200 ML
 - ◊ 12 ML

How to use

- Clean underground from dirt, fat and rust.
- Before use, shake the can vigorously for 3 minutes.
- The spray distance should be approx. 20-30 cm.
- Spray the metallic lacquer in 3 - 5 minute intervals several thin coats.
- Metallic paints have to be sealed after 30 minutes drying time with clear lacquer. Otherwise the aluminium parts in the lacquer will be attacked by environmental and weathering influences.
- Do not spray over synthetic paints!

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

Marking/Labeling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

For any further technical questions call our hotline +49 (0) 62 66 75-266 from Monday to Thursday from 9 h a.m. to 3 h p.m. or on Friday until 12 h p.m.

As of August 18, 2022 – This release replaces all eventually earlier issued versions.

European Aerosols GmbH, Kurt-Vogelsang-Straße 6, 74855 Haßmersheim - info-de@european-aerosols.com
European Aerosols B.V., Wolfraamweg 2, NL-8471 XC Wolvega - info-nl@european-aerosols.com